



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PDIM3WAYWH True 3-Way Dimming Kit

Lutron

Catalog Number	PDIM3WAYWH
Manufacturer	Lutron
Description	Lutron Caseta Smart Dimmer Switch Kit With Remote, 3-Way (2 Points Of Control), Works With Alexa, Apple Homekit, and The Google Assistant, White
Weight per unit	0.9000 (lbs/each)
Product Category	Wiring Devices

### Features

media	Yes
-------	-----

### Material, Color, and Finish

Color	White
Finish	Gloss

### Descriptions

Description	TRUE 3-WAY DIMMING KIT
extra long description	LUT P-DIM-3WAY-WH Cas?ta Dimmer 3-W
Features	Experience the ultimate convenience with the Lutron Caseta wireless dimmer and Pico remote control. The wireless dimmer gives you the ability to set the right light for any activity whether it's reading, watching TV, entertaining, or having a casual dinner. Control your lights in a 3-way application by mounting the Pico remote to the wall with the included Pico wall box bracket, for multi-location dimming. No cutting holes or wiring required! The remote lets you turn lights on/off as well as brighten or di
Long Description	Lutron Caseta Smart Dimmer Switch Kit with Remote, 3-Way (2 Points of Control), Works with Alexa, Apple HomeKit, and the Google Assistant, White
Product Type	Cas?Ta Dimmer 3-Way Kit With Remote

### Manufacturer Information

Brand	Lutron
GTIN	00784276806435
Manufacturers Part Number	P-DIM-3WAY-WH
UPC	784276806435

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
----------------------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.9

## Uses, Certifications, and Standards

Application	Lighting Control
Operating Temperature	32 to 104