



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH50PG 1PH 50VA 120X240V-12X24V 50/60HZ Cu *Hammond Power Solutions*

| | |
|------------------|---|
| Catalog Number | PH50PG |
| Manufacturer | Hammond Power Solutions |
| Description | Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 50va |
| Weight per unit | 3.5 (lbs/each) |
| Product Category | Encapsulated Industrial Contro |

Features

| | |
|---------|----|
| Wattage | 50 |
|---------|----|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.19 |
| Length | 4.38 |
| Width | 3 |

Descriptions

| | |
|------------------------|---|
| Description | 1PH 50VA 120X240V-12X24V 50/60HZ CU |
| extra long description | HMND PH50PG CNTL 50VA 120x240-12x24 |
| Long Description | Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 50VA |
| Product Type | CNTL 50VA 120X240-12X24 |
| Special Features | Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | HPS Imperator™ |
| GTIN | 00803423078126 |
| Manufacturers Part Number | PH50PG |
| UPC | 803423078126 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | CONTROL TRANSFORMERS |
| Type | Tranformer > Dry Type > Control > Molded |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 3.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Automation, Panel shops, Machines, Solenoids, Control Applications, Timers |
| Enclosure | Core and Coil |
| Mounting standard | PANEL |
| Temperature Rating | CSA, UL, CE |
| | Typical 30 Average/ 40 Maximum |