



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH75MQMJ 1PH 75VA 240X480V-120X240V 50/60HZ Cu *Hammond Power Solutions*

| | |
|------------------|--|
| Catalog Number | PH75MQMJ |
| Manufacturer | Hammond Power Solutions |
| Description | Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 75va |
| Weight per unit | N/A |
| Product Category | Encapsulated Industrial Contro |

Features

| | |
|---------|----|
| Wattage | 75 |
|---------|----|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.56 |
| Length | 3.88 |
| Width | 3.25 |

Descriptions

| | |
|------------------------|---|
| Description | 1PH 75VA 240X480V-120X240V 50/60HZ CU |
| extra long description | HMND PH75MQMJ CNTL 75VA 240x480-120 |
| Long Description | Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 75VA |
| Product Type | CNTL 75VA 240X480-120X240 |
| Special Features | Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | HPS Imperator™ |
| GTIN | 00803423077945 |
| Manufacturers Part Number | PH75MQMJ |
| UPC | 803423077945 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | CONTROL TRANSFORMERS |
| Type | Tranformer > Dry Type > Control > Molded |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 0 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Automation, Panel shops, Machines, Solenoids, Control Applications, Timers |
| Enclosure | Core and Coil |
| Mounting standard | PANEL |
| Temperature Rating | CSA, UL, CE |
| | Typical 30 Average/ 40 Maximum |