



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH75MQMJ 1PH 75VA 240X480V-120X240V 50/60HZ Cu *Hammond Power Solutions*

Catalog Number	PH75MQMJ
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 75va
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

Features

Wattage	75
---------	----

Dimensions and Weight

Height	3.56
Length	3.88
Width	3.25

Descriptions

Description	1PH 75VA 240X480V-120X240V 50/60HZ CU
extra long description	HMND PH75MQMJ CNTL 75VA 240x480-120
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 75VA
Product Type	CNTL 75VA 240X480-120X240
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS Imperator™
GTIN	00803423077945
Manufacturers Part Number	PH75MQMJ
UPC	803423077945

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum