

# Eaton PRL2A3600X42CL

Catalog Number: PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V,  
Three-phase, 4W, 600A, 42 circuit, Copper bus

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Pow-R-Stock PRL2A panelboard	PRL2A3600X42CL
<b>UPC</b>	<b>Product Length/Depth</b>
786687011125	85 in
<b>Product Height</b>	<b>Product Width</b>
7 in	18 in
<b>Product Weight</b>	<b>Compliances</b>
75 lb	NEMA Compliant
<b>Certifications</b>	
UL 67	

## Product specifications

### Type

PRL2A Panelboard

### Amperage Rating

600A

### Bus material

Copper

### Bus Rating

600 A

### Feed type

Top/bottom

### Number of circuits

42

### Number Of Poles

Single-pole, three-pole

### Operating Temperature

40°C

### Phase

Three-phase

### Short-circuit rating

35 A

### Wire size

#4 AWG-350 kcmil

### Circuit breaker rating

NEMA

### Current - max

600 A

### NEMA rating

NEMA 1, NEMA 3R

### Series

PRL2a

### Voltage - max

480 V

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL2A3600X42CL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PRL2A3600X42CL

Catalog Number: PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V,  
Three-phase, 4W, 600A, 42 circuit, Copper bus

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Pow-R-Stock PRL2A panelboard	PRL2A3600X42CL
<b>UPC</b>	<b>Product Length/Depth</b>
786687011125	85 in
<b>Product Height</b>	<b>Product Width</b>
7 in	18 in
<b>Product Weight</b>	<b>Compliances</b>
75 lb	NEMA Compliant
<b>Certifications</b>	
UL 67	

## Product specifications

### Type

PRL2A Panelboard

### Amperage Rating

600A

### Bus material

Copper

### Bus Rating

600 A

### Feed type

Top/bottom

### Number of circuits

42

### Number Of Poles

Single-pole, three-pole

### Operating Temperature

40°C

### Phase

Three-phase

### Short-circuit rating

35 A

### Wire size

#4 AWG-350 kcmil

### Circuit breaker rating

NEMA

### Current - max

600 A

### NEMA rating

NEMA 1, NEMA 3R

### Series

PRL2a

### Voltage - max

480 V

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL2A3600X42CL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)