



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC21 20A 120/277VAC B+S Wire DP SW Iv

Pass & Seymour/Legrand

Catalog Number	PS20AC21
Manufacturer	Pass & Seymour/Legrand
Description	2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2200 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Double pole
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Xenon, Incandescent, Halogen, Universal, LED, Fluorescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE DP SW IV
extra long description	P&S PS20AC21 20A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire DP SW I
Special Features	Back & side wire, locking support, heavy duty toggle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007195323
Manufacturers Part Number	PS20AC2I
UPC	785007195323

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC