



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2255 Northwest Parkway SE
30067-0000, GA Marietta
Phone: 678-398-4904
Fax: 678-398-4905



PS20AC2I 20A 120/277VAC B+S Wire DP SW Iv

Pass & Seymour/Legrand

Catalog Number	PS20AC2I
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 2 Poles, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Ivory, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.22 LB
Weight per unit	0.2236 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Double pole
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Xenon, Incandescent, Halogen, Universal, LED, Fluorescent
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	277 VAC, 120 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE DP SW I
extra long description	P&S PS20AC2I 20A 120/277VAC B+S WIR

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195323
Manufacturers Part Number	PS20AC2I
UPC	785007195323



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2255 Northwest Parkway SE
30067-0000, GA Marietta
Phone: 678-398-4904
Fax: 678-398-4905

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2236

Uses, Certifications, and Standards

Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC