



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



PS20AC2W 20A 120/277VAC B+S Wire DP SW WH

Pass & Seymour/Legrand

Catalog Number	PS20AC2W
Manufacturer	Pass & Seymour/Legrand
Description	2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2236 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Double pole
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, Halogen, Incandescent, LED, CFL, Universal, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE DP SW WH
extra long description	P&S PS20AC2W 20A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire DP SW W
Special Features	Back & side wire, locking support, heavy duty toggle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195354
Manufacturers Part Number	PS20AC2-W
UPC	785007195354

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2236

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC