



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS40MBW 400A 600V Male Cam Type PLG Series 16 WH

Pass & Seymour/Legrand

Catalog Number	PS40MBW
Manufacturer	Pass & Seymour/Legrand
Description	Male Cam Device, 400A 600V, Plug White
Weight per unit	0.7440 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	400
Cord Type	Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only
Poles	Single Pole
Voltage	600.0 V
Voltage Rating	600
Wire Size	2/0 - 4/0

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	6.875
------	-------

Descriptions

Description	400A 600V MALE CAM TYPE PLG SERIES 16 WH
extra long description	P&S PS40MBW 400A 600V MALE CAM TYPE
Long Description	Male Cam Device, 400A 600V, Plug White
Product Type	400A 600V Male Cam Type PLG Series 16 WH
Special Features	Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim b

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007308068
Manufacturers Part Number	PS40-MBW
UPC	785007308068



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Cam-Type Series 16 In-Line Connector Male

Trade Size

Amperage	400.0
----------	-------

Packaging

Carton	1
Package	10
Weight Per each	0.744

Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
nema rating	NEMA 3R and 4 for indoor applications
standard	UL, cCSAus