



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT5362LA Duplex Recp Spec GRD 20A/125V La

Pass & Seymour/LeGrand

Catalog Number	PT5362LA
Manufacturer	Pass & Seymour/LeGrand
Description	Plugtail Spec Grade Duplex Receptacle 20AMP 125VOLT Light Almond
Weight per unit	0.2300 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	12

Dimensions and Weight

Height	3.281
Width	.625

Descriptions

Description	DUPLEX RECP SPEC GRD 20A/125V LA
extra long description	P&S PT5362LA DUP RECEPT SPEC GRD 20
Long Description	PlugTail Spec Grade Duplex Receptacle 20amp 125volt Light Almond
Product Type	Dup Recept Spec GRD 20A/125V La
Special Features	Plated steel wrap strap design for maximum durability and corrosion resistance. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Three drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. Crimped and welded contacts. Ultrasonically welded polycarbonate connector housing secures termin



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007091700
Manufacturers Part Number	PT5362-LA
UPC	785007091700

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, cULus UL498
Temperature Rating	-40° - 60° C