



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT8300W Hosp GRD Ehd Duplex Recp 20A/125V WH

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PT8300W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Plugtail Registered Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V Plugtail Registered Devices and Connectors Mean That Device Installation Is The Same Regardless Of Skill Level Of The Installer. The UI-Listed Connectors Are Keyed to Ensure Proper Wiring Installation Into Each Receptacle. |
| Weight per unit | 0.2264 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 12 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .866 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | HOSP GRD EHD DUPLEX RECP 20A/125V WH |
| extra long description | P&S PT8300W HOSP GRD EHD DUP RECEPT |
| Long Description | PlugTail Registered Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. |
| Product Type | Hosp GRD Ehd Dup Recept 20A/125V WH |
| Special Features | Exclusive patented feature, circuit label on face allows permanent circuit identification. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007091168 |
| Manufacturers Part Number | PT8300-W |
| UPC | 785007091168 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.2264 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, cULus UL498, FEDSPEC |