



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918



PV1590EL00 1-1/2IN PVC Coated Rigid

Calpipe Industries, Inc

Catalog Number	PV1590EL00
Manufacturer	Calpipe Industries, Inc
Description	PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard; 8 Standard Package
Weight per unit	4.8 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

Applicable Standard	ANSI C80.1, NEMA RN-1
Bend Angle	90 Degree
Bend Radius	8.25 INCH
End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918

Descriptions

Additional Information	Length 10.6 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mill
Commodity Description	Rigid Conduit Fittings - Steel
Description	1-1/2IN PVC COATED RIGID
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 8 STANDARD PACKAGE; 1-1/2 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 8.25 INCH BEND RADIUS; LENGTH 10.6 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY,
Long Description	PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 8 STANDARD PACKAGE
Product Type	PVC Coated Steel Rigid Conduit Standard Radius Elbow

Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656053918
Manufacturers Part Number	PV1590EL00
Model	PV
UPC	847656053918

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	STANDARD RADIUS

Trade Size

Trade Size	1-1/2 INCH
------------	------------

Packaging

Carton	1
Standard Package	8 W
Weight Per each	4.81

Uses, Certifications, and Standards

Approval	UL 6, CUL
----------	-----------