



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1814RCY Vyl Ins Ring Term *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV1814RCY |
| Manufacturer | Panduit Corporation |
| Description | Ring Terminal, 22 – 18 Awg, 1/4" Stud Size, Vinyl Insulated, Funnel Entry, Standard Package. |
| Weight per unit | 0.3400 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | 18 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Red |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|------|
| Size | 1/4" |
|------|------|

Descriptions

| | |
|------------------------|--|
| extra long description | PAN PV18-14R-CY Pan-Term® PV18-14R- |
| Long Description | Ring Terminal, 22 – 18 AWG, 1/4" stud size, vinyl insulated, funnel entry, standard package. |
| Product Type | Pan-Term® PV18-14R-Cy Loose Piece Ring Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983688562 |
| Manufacturers Part Number | PV18-14R-CY |
| UPC | 074983688562 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Ring Terminal |

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Package | 500 |
| Weight Per each | 0.34 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Enclosure | Ring shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164, CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |