



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PVC3 SCH 40 3" 10' PVC Conduit

*Heritage Plastics*

Catalog Number	PVC3
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 3.008 In Conduit Inner Diameter, 3.500 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 880 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 3 In Trade Size, 0.216 In Wall Thickness, 1.45 LB Weight
Weight per unit	1.5 (lbs/each)
Product Category	PVC Conduit, Fittings, & Boxes

### Features

Material	PVC
outside diameter	3.5

### Dimensions and Weight

Diameter	3"
Height	3.5
Width	3.5

### Descriptions

Description	SCH 40 3" 10' PVC CONDUIT
extra long description	AL-TUBE 8112 PVC SCH40 3 x 10 UL BE

### Manufacturer Information

GTIN	00091111081125
Manufacturers Part Number	A52DA12
UPC	091111081125

### Taxonomies, Classifications, and Categories

Category Description	Conduit & Raceways - Pvc Conduit, Fittings, & Boxes PVC Schedule 40 Conduit
Type	PVC - Sch 40/80

### Availability

minimum qty	10
-------------	----

### Packaging

Carton	10
Package	880
Weight Per foot	1.45



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

standard

UL651

---