

Eaton QB1030GF

Catalog Number: QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB

General specifications



Photo is representative

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QB1030GF
UPC	Product Length/Depth
786680222429	4 in
Product Height	Product Width
1 in	3.5 in
Product Weight	Warranty
0.45 lb	1 year
Compliances	Certifications
Contact Manufacturer	UL 489

Physical Attributes

Circuit breaker type

QB

Connection

Bolt-on

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-4 AWG

Performance Ratings

Amperage Rating

30 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - QB1030GF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)