

Specifications

Photo is representative

Eaton QB1030GF

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,30A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QB1030GF
UPC	786680222429
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	1 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL 489
PRODUCT TYPE	GFCI circuit breakers

Physical Attributes

CIRCUIT BREAKER TYPE	QB
CONNECTION	Bolt-on
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-4 AWG

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
QB1030GE](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

