

Specifications

Eaton QBGFEP2050

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,50A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,30 mA Trip sensitivity,QBGFEP

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2050
UPC	786679145203
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	4.4 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated

Physical Attributes

CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

Miscellaneous

SPECIAL FEATURES	Bolt-on mounting
-------------------------	------------------

Performance Ratings

AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	30 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources

CATALOGS

[Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - QBGFEP2050](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

