

Eaton QBGFT1030

Catalog Number: QBGFT1030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFT1030
UPC	Product Length/Depth
786680130984	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.5 lb	1 year
Certifications	
UL 489	

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#10 Cu, #8 Al

Performance Ratings

Amperage Rating

30 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBGFT1030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)