

# Specifications

Photo is representative



## Eaton QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#8 Cu #8-6 Al

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT1040
<b>UPC</b>	786680130991
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489

**EATON**

Powering Business Worldwide

# Specifications

Photo is representative



## Eaton QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#8 Cu #8-6 Al

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT1040
<b>UPC</b>	786680130991
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489

**EATON**

Powering Business Worldwide