

# Specifications

Photo is representative

## Eaton QBGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#14-10 AWG Cu #12-10 AWG Al

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT2020
<b>UPC</b>	786676026710
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.6 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide

# Specifications

Photo is representative

## Eaton QBGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
---------------------	-------------------------------

<b>WIRE SIZE</b>	#14-10 AWG Cu #12-10 AWG Al
------------------	--------------------------------

<b>CATALOG NUMBER</b>	QBGFT2020
-----------------------	-----------

<b>UPC</b>	786676026710
------------	--------------

<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
-----------------------------	--------

<b>PRODUCT HEIGHT</b>	2 in
-----------------------	------

<b>PRODUCT WIDTH</b>	2.75 in
----------------------	---------

<b>PRODUCT WEIGHT</b>	0.6 lb
-----------------------	--------

<b>WARRANTY</b>	1 year
-----------------	--------

<b>CERTIFICATIONS</b>	UL 489
-----------------------	--------

<b>CATALOG NOTES</b>	HACR rated
----------------------	------------



Powering Business Worldwide