

Specifications

Photo is representative

Eaton QBGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2020
UPC	786676026710
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Performance Ratings	
AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2020

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

