

Specifications

Photo is representative

Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#6-4 Al #8-6 Cu

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Powering Business Worldwide

Specifications

Photo is representative

Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#6-4 Al #8-6 Cu

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Powering Business Worldwide