

# Specifications

## Eaton QBHGFT2020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,22 kAIC,Two-pole,120/240V,QBHGF



Photo is representative



### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT2020
UPC	786676027823
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHGF
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker

## Performance Ratings

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>VOLTAGE RATING</b>	120/240 V

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBHGFT2020</a>
--------------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

