

# Specifications

## Eaton QBHGFT2020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,22 kAIC,Two-pole,120/240V,QBHGF



Photo is representative



### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT2020
UPC	786676027823
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

## Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
VOLTAGE RATING	120/240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHGF2020</a>
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

