

Eaton QBHW1015

Catalog Number: QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW



General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW1015
	UPC
	786679392003
Product Length/Depth	Product Height
3.9 in	4.8 in
Product Width	Product Weight
1.2 in	0.3 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Catalog Notes

Switching duty rated for 120V fluorescent light applications, HACR rated

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

15 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1015](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBHW1015

Catalog Number: QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW



General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW1015
	UPC
	786679392003
Product Length/Depth	Product Height
3.9 in	4.8 in
Product Width	Product Weight
1.2 in	0.3 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Catalog Notes

Switching duty rated for 120V fluorescent light applications, HACR rated

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

15 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1015](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)