

# Eaton QBHW1015

Catalog Number: QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB thermal magnetic circuit breaker	QBHW1015
	UPC
	786679392003
<b>Product Length/Depth</b>	<b>Product Height</b>
3.9 in	4.8 in
<b>Product Width</b>	<b>Product Weight</b>
1.2 in	0.3 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	CSA Certified

## Catalog Notes

Switching duty rated for 120V fluorescent light applications, HACR rated

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

15 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

17

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW1015](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)