

Specifications



Eaton QBHW1020

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 20A, 22 kAIC, 120/240V

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1020
UPC	786679392058
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	1.2 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Switching duty rated for 120V fluorescent light applications, HACR rated

