

Eaton QBHW1040

Catalog Number: QBHW1040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 40A, 22 kAIC, 120/240V

General specifications



Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW1040
	UPC
	786679392256
Product Length/Depth	Product Height
3.6 in	4.7 in
Product Width	Product Weight
1.2 in	0.3 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag

Performance Ratings

Amperage Rating

40 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)