

Specifications

Eaton QBHW1050

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 70 A, 22 kAIC, Single-pole, 120/240 V, Non-interchangeable, QBHW



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1050
UPC	786679392300
PRODUCT LENGTH/DEPTH	3.6 in
PRODUCT HEIGHT	3.2 in
PRODUCT WIDTH	1.2 in
PRODUCT WEIGHT	0.35 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

Miscellaneous

QUANTITY	17
----------	----

Performance Ratings

AMPERAGE RATING	50 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW1050
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

