



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW2015 2 Pole 15A QBHW BRKR

Eaton Corp

Catalog Number	QBHW2015
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-Pole, 15A, 22 Kaic, 120/240V , Bolt-On
Weight per unit	0.5500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 2.1000 IN X 4.8000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	2 POLE 15A QBHW BRKR
extra long description	ETN QBHW2015 2 Pole 15 Amp QBHW Bre
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 15A, 22 kAIC, 120/240V , Bolt-on
Product Type	2 Pole 15 Amp QBHW Breaker

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679392508
Manufacturers Part Number	QBHW2015
UPC	786679392508

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment - Other

standard

UL Listed,CSA Certified