

Specifications



Eaton QBHW2030

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 35 A, 22 kAIC, Two-pole, 240 V, Non-Interchangeable, Q7, QBHW

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2030
UPC	786679392652
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.3 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	HACR rated



Powering Business Worldwide