

Specifications



Eaton QBHW2060

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 60A, 22 kAIC, 120/240V , Bolt-on

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2060
UPC	786679392904
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.3 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

Miscellaneous

QUANTITY	7
----------	---

Performance Ratings

AMPERAGE RATING	60 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW2060

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

