

# Specifications



## Eaton QBHW2100

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 100A, 22 kAIC, 120/240V , Bolt-on

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Quicklag

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW2100
<b>UPC</b>	786679393109
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.2 in
<b>PRODUCT WEIGHT</b>	0.8 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide

# Specifications



## Eaton QBHW2100

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 100A, 22 kAIC, 120/240V , Bolt-on

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Quicklag

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW2100
<b>UPC</b>	786679393109
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.2 in
<b>PRODUCT WEIGHT</b>	0.8 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide