

# Specifications

## Eaton QBHW3020H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 20A, 22 kAIC, 240V, Bolt-on

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW3020H
<b>UPC</b>	786679393208
<b>PRODUCT LENGTH/DEPTH</b>	3.8 in
<b>PRODUCT HEIGHT</b>	4.7 in
<b>PRODUCT WIDTH</b>	3.2 in
<b>PRODUCT WEIGHT</b>	1.1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	HACR rated

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Quicklag

## Miscellaneous

<b>QUANTITY</b>	32
-----------------	----

## Performance Ratings

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>VOLTAGE RATING</b>	240 V - 240 V

## Resources

<b>CATALOGS</b>	<a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBHW3020H</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

