

Specifications



Eaton QBHW3030H

Quicklag Industrial
Thermal-Magnetic Circuit
Breaker, Three-pole, 30A,
22 kAIC, 240V, Bolt-on

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW3030H
UPC	786679393307
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	3.2 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	HACR rated



Powering Business Worldwide

Specifications



Eaton QBHW3030H

Quicklag Industrial
Thermal-Magnetic Circuit
Breaker, Three-pole, 30A,
22 kAIC, 240V, Bolt-on

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three- pole
TYPE	Quicklag

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW3030H
UPC	786679393307
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	3.2 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	HACR rated



Powering Business Worldwide