

# Specifications



## Eaton QBHW3030H

Quicklag Industrial  
Thermal-Magnetic Circuit  
Breaker, Three-pole, 30A,  
22 kAIC, 240V, Bolt-on

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Quicklag

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW3030H
<b>UPC</b>	786679393307
<b>PRODUCT LENGTH/DEPTH</b>	3.8 in
<b>PRODUCT HEIGHT</b>	4.7 in
<b>PRODUCT WIDTH</b>	3.2 in
<b>PRODUCT WEIGHT</b>	1.1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide