

Specifications

Eaton QC2010

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 10 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC2010
UPC	786679309285
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.65 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QC
CONNECTION	Cable-in/cable-out
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	10 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC2010
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton QC2010

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 10 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC2010
UPC	786679309285
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.65 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QC
CONNECTION	Cable-in/cable-out
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	10 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC2010
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

