

Specifications



Eaton QCD2060

Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCD, Non-interchangeable

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton QC thermal magnetic circuit breaker |
| CATALOG NUMBER | QCD2060 |
| UPC | 786679135969 |
| PRODUCT LENGTH/DEPTH | 4 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2 in |
| PRODUCT WEIGHT | 0.905 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL Listed CSA Certified |



Powering Business Worldwide

Physical Attributes

| | |
|-----------------------------|----------------------------|
| CIRCUIT BREAKER TYPE | QCD |
| CONNECTION | Cable-in/cable-out |
| NUMBER OF POLES | Two-pole |
| TYPE | Industrial circuit breaker |

Performance Ratings

| | |
|-------------------------|-----------|
| AMPERAGE RATING | 60 A |
| INTERRUPT RATING | 10 kAIC |
| TRIP TYPE | T268 |
| VOLTAGE RATING | 120/240 V |

Miscellaneous

| | |
|----------------|---------------------|
| OPTIONS | Non-interchangeable |
|----------------|---------------------|

Resources

| | |
|--------------------------------------|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QCD2060 |
|--------------------------------------|---|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

