

Specifications



Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

General specifications

PRODUCT NAME	Eaton QCR thermal magnetic circuit breaker
CATALOG NUMBER	QCR2030
UPC	786679144343
PRODUCT LENGTH/DEPTH	4.6 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
COMPLIANCES	HACR Rated
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Standard breaker terminals are box type lugs.



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QCR
CONNECTION	Cable-in/cable-out
MOUNTING METHOD	Rear
NUMBER OF POLES	Two-pole
TERMINALS	Fixed
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - QCR2030](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

General specifications

PRODUCT NAME	Eaton QCR thermal magnetic circuit breaker
CATALOG NUMBER	QCR2030
UPC	786679144343
PRODUCT LENGTH/DEPTH	4.6 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
COMPLIANCES	HACR Rated
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Standard breaker terminals are box type lugs.



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QCR
CONNECTION	Cable-in/cable-out
MOUNTING METHOD	Rear
NUMBER OF POLES	Two-pole
TERMINALS	Fixed
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - QCR2030](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

