

# Specifications

## Eaton RACH24L125I



Photo is representative

Eaton CH 3/4-inch Loadcenter Retrofit  
Stocking Kit,Main lug only,125 A,size group  
a,Cover height: 33 in,Cover width: 24  
in,NEMA 1,CH,Surface,flush,24  
Circuits,Single-phase,0.75 in,#4-2/0 AWG

### General specifications

PRODUCT NAME	Eaton CH retrofit kit
CATALOG NUMBER	RACH24L125I
UPC	786685211060
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	30 in
PRODUCT WIDTH	22 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
CERTIFICATIONS	UL 67
CATALOG NOTES	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



### Product specifications

TYPE	Retrofit kit
------	--------------

### Resources

MULTIMEDIA	<a href="#">AFCI Educational Video</a>
------------	--

AMPERAGE RATING	125 A
MAIN CIRCUIT BREAKER	CH
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	24
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG
BOX SIZE	Retro size group a
COVER HEIGHT	33
COVER WIDTH	24
ENCLOSURE	NEMA 1

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RACH24L125I</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications

## Eaton RACH24L125I



Photo is representative

Eaton CH 3/4-inch Loadcenter Retrofit  
Stocking Kit, Main lug only, 125 A, size group  
a, Cover height: 33 in, Cover width: 24  
in, NEMA 1, CH, Surface, flush, 24  
Circuits, Single-phase, 0.75 in, #4-2/0 AWG

### General specifications

PRODUCT NAME	Eaton CH retrofit kit
CATALOG NUMBER	RACH24L125I
UPC	786685211060
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	30 in
PRODUCT WIDTH	22 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
CERTIFICATIONS	UL 67
CATALOG NOTES	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



### Product specifications

TYPE	Retrofit kit
------	--------------

### Resources

MULTIMEDIA	<a href="#">AFCI Educational Video</a>
------------	--

AMPERAGE RATING	125 A
MAIN CIRCUIT BREAKER	CH
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	24
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG
BOX SIZE	Retro size group a
COVER HEIGHT	33
COVER WIDTH	24
ENCLOSURE	NEMA 1

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RACH24L125I</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

