



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RB400300 4" X 3" Reducing Bushing

*Appleton/Oz Gedney*

Catalog Number	RB400300
Manufacturer	Appleton/Oz Gedney
Description	Reducing Bushing, Size: 4 X 3 In, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class Ii: Groups E, F, G, Class Iii, UI 886 (1203), UI E10444, Csa C22.2 No. 25, C22.2 No. 30, Csa 0651
Weight per unit	0.8000 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	NPT
Material	Steel

### Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

### Dimensions and Weight

Size	4 x 3
------	-------

### Descriptions

Description	4" X 3" REDUCING BUSHING
extra long description	APP RB400-300 RDC BUSH MALL 4TO3 IN
Long Description	Reducing Bushing, Size: 4 X 3 IN, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886 (1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA 0651
Product Type	RDC Bush Mall 4TO3 In NPT
Special Features	Smooth rounded integral bushing protects conductor insulation

### Manufacturer Information

Brand	Appleton
GTIN	00781381655750
Manufacturers Part Number	RB400-300
UPC	781381655750

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Reducing Bushing

### Packaging

Carton	2
Package	10
Weight Per each	0.8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Reducing Conduit Entries To A Smaller Size In Threaded Rigid  
And IMC Conduit Systems

standard

Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886  
(1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA 065181