



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD113W Radiant 3 Switch SP/3-Way + SP + SP WH

Pass & Seymour/LeGrand

Catalog Number	RCD113W
Manufacturer	Pass & Seymour/LeGrand
Description	Two Single Pole Switch, 3 Poles, 3 Ways, 15 A, 120/125 V Ac, Stainless Steel, White, Rocker Actuator, Box Mount, 1.29 (L) X 1.59 (W) X 3.81 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.21 LB
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Load Rating	15 A @ 120/125 VAC
Load Type	Halogen, Incandescent, LED, Universal, Xenon, CFL, Fluorescent
media	Yes
Number of Gangs	1.0
Number of Switches	3.0
operating cycles	50000
Poles	1, 3-Way
Switch Type	Paddle
throw type	Single Throw
Voltage	120 VAC, 125 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	SATIN
--------	-------

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT 3 SWITCH SP/3-WAY + SP + SP WH
extra long description	P&S RCD113W RADIANT 3 SWITCH, SP/3-

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054774
UPC	785007054774



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	12
Weight Per each	0.2083

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	UL, CULUS, cULus, UL Listed