



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 Commerce Rd
71601-7613, AR Pine Bluff
Phone: 870-671-4805
Fax: 870-671-4806



RCD111 Radiant 2 Switch SP + SP Iv

Pass & Seymour/Legrand

Catalog Number	RCD111
Manufacturer	Pass & Seymour/Legrand
Description	Two Single Pole Switch, 1 Pole, 15 A, 120/125 V Ac, Stainless Steel, Ivory, Rocker Actuator, Box Mount, 1.29 (L) X 1.59 (W) X 3.81 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.21 LB
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Load Rating	15 A @ 120/125 VAC
Load Type	Xenon, Universal, Halogen, Incandescent, CFL, Fluorescent, LED
media	Yes
Number of Gangs	1.0
Number of Switches	2.0
operating cycles	50000
Poles	3-Way, 1
Switch Type	Paddle
throw type	Single Throw
Voltage	120 VAC, 125 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	SATIN
--------	-------

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT 2 SWITCH SP + SP IV
extra long description	P&S RCD111 RADIANT 2 SWITCH, SP + S

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054842
UPC	785007054842



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 Commerce Rd
71601-7613, AR Pine Bluff
Phone: 870-671-4805
Fax: 870-671-4806

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	12
Weight Per each	0.2083

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	UL, CULUS, cULus, UL Listed