

RDL-BF



TECHNICAL SPECIFICATIONS:

- :: Die-cast aluminum with white powder coat finish
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: 0.125" white translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working voltage: 120V AC
- :: Dimmable
- :: LED: EPISTAR chip (COB) and driver—35,000-hour design life
- :: Power factor: 90% +
- :: Suitable for damp locations when gasket is used
- :: Maximum Ambient Temperature: 104°F
- :: 5-year warranty
- :: UL-listed



LED DOWNLIGHTS (BAFFLE TRIM)—4" & 5" / 6" ROUND

CATALOG NO.	WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-BF-27K	11W	2700K	650LM	4"
RDL4-BF-30K	11W	3000K	700LM	
RDL4-BF-41K	11W	4100K	750LM	
RDL4-BF-50K	11W	5000K	800LM	
RDL6-BF-27K	13W	2700K	850LM	5" / 6"
RDL6-BF-30K	13W	3000K	900LM	
RDL6-BF-41K	13W	4100K	950LM	
RDL6-BF-50K	13W	5000K	1000LM	



RDL-BF



TECHNICAL SPECIFICATIONS:

- :: Die-cast aluminum with white powder coat finish
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: 0.125" white translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working voltage: 120V AC
- :: Dimmable
- :: LED: EPISTAR chip (COB) and driver—35,000-hour design life
- :: Power factor: 90% +
- :: Suitable for damp locations when gasket is used
- :: Maximum Ambient Temperature: 104°F
- :: 5-year warranty
- :: UL-listed



Includes medium base
E-26 screw-in adaptor
that fits any standard
incandescent downlight

LED DOWNLIGHTS (BAFFLE TRIM)—4" & 5"/6" ROUND

CATALOG NO.	WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-BF-27K	11W	2700K	650LM	4"
RDL4-BF-30K	11W	3000K	700LM	
RDL4-BF-41K	11W	4100K	750LM	
RDL4-BF-50K	11W	5000K	800LM	
RDL6-BF-27K	13W	2700K	850LM	5"/6"
RDL6-BF-30K	13W	3000K	900LM	
RDL6-BF-41K	13W	4100K	950LM	
RDL6-BF-50K	13W	5000K	1000LM	

