

# Specifications

Photo is representative



## Eaton REN-40

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 40 A, Class H, Non-indicating, 10 kAIC, Standard, 10, 250 V

### Electrical rating

<b>AMPERAGE RATING</b>	40 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>VOLTAGE RATING</b>	250 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series REN fuse
<b>CATALOG NUMBER</b>	REN-40
<b>UPC</b>	051712100403
<b>EAN</b>	5027590182386
<b>PRODUCT LENGTH/DEPTH</b>	0.82 in
<b>PRODUCT HEIGHT</b>	2.98 in
<b>PRODUCT WIDTH</b>	0.82 in
<b>PRODUCT WEIGHT</b>	0.12 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Not Applicable

**EATON**

Powering Business Worldwide