

Specifications

Photo is representative



Eaton REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

Electrical rating

AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

General specifications

PRODUCT NAME	Eaton Bussmann series REN fuse
CATALOG NUMBER	REN-50
UPC	051712100502
EAN	5027590465793
PRODUCT LENGTH/DEPTH	0.82 in
PRODUCT HEIGHT	2.98 in
PRODUCT WIDTH	0.82 in
PRODUCT WEIGHT	0.12 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable

EATON

Powering Business Worldwide

Specifications

Photo is representative



Eaton REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

Electrical rating

AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

General specifications

PRODUCT NAME	Eaton Bussmann series REN fuse
CATALOG NUMBER	REN-50
UPC	051712100502
EAN	5027590465793
PRODUCT LENGTH/DEPTH	0.82 in
PRODUCT HEIGHT	2.98 in
PRODUCT WIDTH	0.82 in
PRODUCT WEIGHT	0.12 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable

EATON

Powering Business Worldwide