

Specifications

Eaton REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications

PRODUCT NAME	Eaton Bussmann series REN fuse
CATALOG NUMBER	REN-60
UPC	051712100601
PRODUCT LENGTH/DEPTH	0.82 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	1.4 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

CATALOGS	REN-60~SUPER LAG RENEWABLE FUSE 60/250
	Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - REN-60

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

