



RH1BUDC24V Relay Plug-In SPDT 10A 24VDC

Idec

Catalog Number	RH1BUDC24V
Manufacturer	Idec
Description	Plug-In Relay, Industrial Application, Plug-In Connection Type, SPDT Contact Configuration, Silver Cadmium Oxide Contact Material, 10 A Current Rating, Made In Usa, Plug In Mount Mounting Type, 42 MM Overall Height, 14 MM Overall Length, 27.5 MM Overall Width, 1 Va (60HZ);Ac:1.1 Va (50HZ);DC:0.8 W Power Rating, RH Series, Rectangular Shape, Ce Certified;Cru Us;Csa Certified;Rohs Compliant;Tuv Standards Met, Blade Terminal Type, 24 V DC Voltage Rating, 24 G Weight
Weight per unit	0.1500 (lbs/each)
Product Category	General Purpose Power Relays

Descriptions

Description	RELAY PLUG-IN SPDT 10A 24VDC
-------------	------------------------------

Taxonomies, Classifications, and Categories

Category Description	IDECLAY RELAYS.IDC
----------------------	--------------------

Packaging

Carton	1
Package	10
Weight Per each	0.15