



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Rotary Dimmer

RI06P-W

UPC:032664699023

### Dimensions:

- **Height:** 4.75 IN
- **Length:** 2.3 IN
- **Width:** 3.06 IN

**Weight:** .24 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Power failure memory, with preset
- **Allowable Wire Size:** #16 AWG
- **Amperage Rating:** 5A
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Closure Type:** Maintained
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen
- **Operating Temperature:** 0° to 40°C
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 600W

**Supporting documents:** No Data

### Certifications:

- NOM
- cULus Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Rotary Dimmer

RI06P-W

UPC:032664699023

### Dimensions:

- **Height:** 4.75 IN
- **Length:** 2.3 IN
- **Width:** 3.06 IN

**Weight:** .24 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Power failure memory, with preset
- **Allowable Wire Size:** #16 AWG
- **Amperage Rating:** 5A
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Closure Type:** Maintained
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen
- **Operating Temperature:** 0° to 40°C
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 600W

**Supporting documents:** No Data

### Certifications:

- NOM
- cULus Listed

**Product compliance:** No Data



