



RX82WGPCS 8/2 WG Romex-Pieces

Southwire Company



Catalog Number	RX82WGPCS
Manufacturer	Southwire Company
Description	Non-Metallic Sheathed Cable, Color-Coded Cable Jacket Additional Information, Dry Location; Residential Application, Copper Conductor Material, 8 Awg Conductor Size, 40 A Current Rating, Polyvinyl Chloride (PVC) Insulation Material, 35 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 2 - Conductors, 7 - Strands, 618 Mil Overall Length, Reel Package Type, Strand Solid/Strand, Astm B-3 and B-8;Federal Specification A-A-59544;Nfpa 70;Reach/Rohs Compliant;UI 71
Weight per unit	0.1880 (lbs/ft)
Product Category	NM-B - NMD90

Descriptions

Also Known As...	Non-Metallic Sheathed Cable 220 Wire Thermoplastic-Sheathed Cable
Description	8/2 WG ROMEX-PIECES

similar brands
Romex®

Manufacturer Information

Brand	Copper
-------	--------

Taxonomies, Classifications, and Categories

Category Description	ROMEX (RX)& UF CABLE
----------------------	----------------------

Packaging

Carton	1
Weight Per foot	0.188